

## *Simplicity*<sup>®</sup> PS-LED-010 Applications for Advance Xitanium<sup>™</sup> LED Driver

	Product Code	Model Number	General Description
120V Applications	72510	PS-LED-010-IV-120V	Preset slide, controls 0-10 VDC LED driver, single pole or 3-way, ivory or white, 120V.
	72511	PS-LED-010-WH-120V	
	72512	PS-LED-010-3W-IV-120V	
	72513	PS-LED-010-3W-WH-120V	

### Typical Driver Information:

	Xitanium Driver	Power Supply Output Power	Circuit Volts 60Hz	Control Voltage	Maximum # of Drivers controlled by PS-LED
<b>120V Applications</b>	LED120A0024V10D	25W	120V	24V	23

#### Tech Notes:

- The HUNT PS-LED series 0-10 VDC controller has a maximum input voltage of 8.5 amps (120V) or 3.7 amps (277V).
- A reference voltage must be supplied by the LED driver for proper functionality.
- The total run length of low voltage control wiring should not exceed 500 feet.
- A separate neutral is required for each dimmed circuit.
- All NEC guidelines and local codes must be followed.
- Consult with the driver manufacturer for application and installation guidelines.

Advance Xitanium<sup>™</sup> is a registered trademark of Advance Transformer Co.